# Shower/Toilet Lifter

A high quality lifter designed to assist people with weak leg muscles to stand and sit unassisted from a normal toilet. As it is mobile, it has many other applications. Ideal for people with neuro-muscular disabilities, MS or severe arthritis. Manufactured by TA Services, a specialist mobility and rehab company.





1) Keep knees at a 90° angle



 Start lifting and move forwards on the seat always keeping your entire feet on the ground



Lift until legs are fully stretched standing upright

## Lift, Don't Tilt

## User feels safer

It has been proven that with a vertical lift a person using the correct technique feels safer, whereas a tilt action may make them anxious, as maintaining balance is more difficult.

See the above diagram for the correct technique with a Toilet lifter from seated to standing position.

## Mobile with Many Applications

#### When user is tired

Its primary function is for use over the toilet. However, it is also waterproof, ideal for use in an open wet area shower. The shower/toilet lifter may also be used as a mobile transit chair to assist transfers from bed and wheelchair or as a commode at night time.

## Cost Effective

## Quality ensures longer economic life

Manufactured from high quality stainless steel, easily cleaned and designed to last in excess of 10 years, ensures a cost effective acquisition.

## Easy to Install

## Designed for Reissue

Very manoeuvrable and requires only a small amount of space. Installed from the front and easy to move for cleaning or to another location if required.



# Assistive Living Technologies & Equipment Resources

## 03 9922 0372

## Specifications

Frame

Art no.:

ISO Classification:

Specifications		
User weight max.		120 kg
Seat height		48-88 cm
Lifting interval continuously variable		40 cm
Seat width	•	42 cm
Seat depth		41 cm
Backrest height		34-46 cm
Armrest height		23 cm
Distance between armrests		49 cm
Legrest height		31-51 cm
Total width		63 cm
Total height	10	05-145 cm
Turn diameter, min	1	100 cm
Wheels	10 cm with individ	dual brake
Weight		32 kg
Batteries	2x12V, maintenancefree	
Batterycapacity	Appr	ox. 60 lifts
	of 60 kg for eacl	h charging
Charging alarm		Acoustic
Materials		
Seat	U	rea plastic

Powder coated stainless steel

ISO 12 36 06

30026